

NEW HeadStar Pro

4 x AA - Proximity Distance Dimming LED Head Torch, 850 lumens

The HeadStar Pro uses advanced reactive distance sensors, which automatically adjusts from spot (long distance) to flood (closeup) beam according to its surroundings. Complete with two warm side lights for longer runtimes in low lighting and red, blue or green rear lights.



Non Rechargeable
Powered By 4X AAA Alkaline Batteries



REAR LIGHTS

Red, Blue or Green choose from High or Flashing mode



KEY FEATURES:

- 850 Lumens
- 550 metre beam
- Runs up to 50 hours
- Wide flood beam
- Narrow long distance beam
- Powered by 4 x AA Alkaline batteries
- 180° beam angle adjustment
- Adjustable headband
- Helmet mountable with clips

	BOOST	NARROW HIGH	NARROW LOW	WIDE HIGH	WIDE LOW
LIGHT OUTPUT	850 LUMENS	620 LUMENS	45 LUMENS	590 LUMENS	37 LUMENS
Beam	550 METRES	500 METRES	169 METRES	5 METRES	169 METRES
RUN TIMES	2hrs 45MIN	4hrs	50hrs	4hrs	50hrs
4 XAA	IPX4 RATING		DIMENSIONS 46mm x85mm x39mm		291g

PRODUCT CODE: NSHEADSTAR-PRO



PROXIMITY DIMMING
Automatically changes from (Long distance) **NARROW** to **WIDE** (Close up applications).



180° beam angle adjustment



SAFETY LOCK

Prevents accidental power loss during storage or transportation.



BRIGHTNESS MEMORY FUNCTION

Previous brightness level will be memorised and resume when turned on.



WHITE SIDE LIGHTS
for low level lighting.



Optional accessories:



Helmet Clips:
SPPCLIPS