

ARCA 203015T No MP



Sample image

Order symbol : ARCA 203015T No MP

Product nr : 8121020N

Description : Cabinet, PC

Remarks : Transparent cover, 1-point locking, hinges on the short side, without mountingplate

EAN : 6418074318626

El. number :

- Finland : 3425137
- Denmark : 8212056307
- Sweden : 2506793

Including : Cabinet base, door with PUR gasket. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

8121020N_FIBOX ARCA IEC 203015T

Dimensions :	Height	Width	Depth
mm :	200	300	150
inch :	7.87	11.81	5.91

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	Smoked grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

MPMP ARCA 3020	Mounting plate multiperforated (250x150x2 mm - ø3.6 mm) (250 x 150 x 1.5)
IDS ARCA 2030	Inner door set
MPP ARCA 2030	Mounting plate perforated (250x150x2 mm - 26x11 mm) (150 x 250 x 2)
MPS ARCA 3020	Mounting plate (250x150x2 mm) (250 x 150 x 2)
DRS ARCA 203015	DIN rail frame set (285 x 185 x 35)
RCS ARCA 2030	Rain canopy set for size 2030 (30 x 300 x 20)
PMK ARCA 30	PoleMounting kit, for pole ø100-300mm (385 x 285 x 35)
MPX ARCA 3020	Mounting plate (250x150 mm) (250 x 150 x 5)

Ratings :

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK09;
electrical_insulation :	Totally insulated

Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C
UL Type	1, 4, 4X, 12, 13

Certificates :
Certificate FI 40467