

Datasheet

76 Piece Metrinch Socket & Combi Spanner Set

RS Stock number [479-5718](#)



Features:

1/4, 3/8 and 1/2 in. combined socket and combination spanner set, equivalent to a 135 piece traditional set. Manufactured from chrome vanadium high quality steel, all sockets conform to DIN 3124, ratchets and accessories to DIN 3122 and 3123

Metrinch® tools are designed to drive on the hexagon flats, not the corners. This enables one tool to drive Metric and A/F, BSW and BSF fasteners. This unique drive system also makes these tools particularly useful for use on old and rounded off hexagon nuts and bolts

Set is supplied complete in a heavy duty blow moulded plastic carrying case



Kit Contents	
1/4 in. Sockets (Standard)	5, 6, 7, 8, 9, 10, 11, 12, 13 mm
1/4 in. Sockets (Deep Wall)	5, 6, 7, 8, 9, 10, 11, 12mm
3/8 in. Sockets	10, 11, 12, 13, 14, 15, 16, 17, 19, 20, 21 , 22mm
3/8 in. Sockets (Deep Wall)	10, 11, 13, 14, 17, 19, 22mm
1/2 in. Sockets	10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 25, 26, 27 , 29, 30 , 31, 32 mm
Combination Spanners	10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21mm
Sparkplug Sockets	16 & 20mm
Ratchets	3/8 in – 40 teeth and 1/2 in – 40 teeth
Breaker Bar	-
Extensions	1/4 in x 50mm, 3/8 in x 75mm, 1/2 in x 250mm
Sliding Tee	1/2 in
Adaptor	1/4 in male to 3/8 in female
Universal Joint	1/4 in (Joint), 3/8 in
Spinner Handle	1/4 in