

Features

- High melting point nylon 66
- Good electrical characteristics
- High chemical resistance
- Impact resistant
- Easily machined to make gears
- Comes in white colour

RS PRO White Nylon Rod, 500mm x 150mm Diameter

RS Stock No.: 514-455



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO nylon rod in white colour, measures 500 mm long with a diameter of 150 mm. This hot melting nylon rod possess self-lubricating qualities with a good electrical characteristics. It offers high resistance to chemical, abrasion and UV lights.

General Specifications

Colour	White
Flammability Rating	UL HB
Form	Rod
Hardness	170 Ball Indentation
Material	Nylon
Density	1.14 g/cm ³
Elongation	150%
Length	500 mm
Maximum Operating Temperature	+170°C
Rod Diameter	150 mm
Water Absorption	8.5%
Tensile Strength	60 MPa (Wet), 80 MPa (Dry)
Features	<ul style="list-style-type: none"> • High melting point nylon 66 • Good electrical characteristics • High chemical resistance • Impact resistant • Easily machined to make gears • Comes in white colour