

M12 IR-201B 3/8 | M12™ sub compact ratchet



- Pneumatic performance with cordless convenience, 47 Nm of torque and no load speed of 250 rpm
- REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability
- Reinforced housing - provides high durability similar to steel ratchets
- Compact design - ideal for tight spaces and small engine bays
- Variable speed metal paddle switch trigger - provides greater user control during application
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- On board fuel gauge and LED light - added user convenience and illumination in low lit working conditions

Tool reception	3/8" square
Max. torque (Nm)	47
No load speed (rpm)	0 - 250
Length (mm)	274
Weight with battery pack (kg)	0.9
Kit included	1 x M12 B2 Battery pack, C12 C Charger, Tool bag
Article Number	4933441720