


SIPMOS® Power-Transistor
Features

- P-Channel
- Enhancement mode
- Avalanche rated
- dv/dt rated
- 175°C operating temperature
- Pb-free lead finishing; RoHS compliant
- ° Halogen-free according to IEC61249-2-21
- ° Qualified according to AEC Q101


Product Summary

V_{DS}	-60	V
$R_{DS(on),max}$	0.3	Ω
I_D	-8.8	A

PG-TO263-3


Type	Package	Tape and reel information	Marking	Lead free	Packing
SPB08P06PG	PG-TO263-3	1000 pcs / reel	08P06P	Yes	Non dry

Maximum ratings, at $T_j=25\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
			steady state	
Continuous drain current	I_D	$T_A=25\text{ °C}$	-8.8	A
		$T_A=100\text{ °C}$	-6.3	
Pulsed drain current	$I_{D,pulse}$	$T_A=25\text{ °C}$	-35.32	
Avalanche energy, single pulse	E_{AS}	$I_D=8.83\text{ A}$, $R_{GS}=25\text{ }\Omega$	70	mJ
Reverse diode dv/dt	dv/dt	$I_D=8.83\text{ A}$, $V_{DS}=48\text{ V}$, $di/dt=-200\text{ A}/\mu\text{s}$, $T_{j,max}=175\text{ °C}$	-6	kV/ μs
Gate source voltage	V_{GS}		± 20	V
Power dissipation	P_{tot}	$T_A=25\text{ °C}$	42	W
Operating and storage temperature	T_j , T_{stg}		"-55 ... +175"	°C
ESD class				
Soldering temperature			260 °C	
IEC climatic category; DIN IEC 68-1			55/150/56	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal characteristics						
Thermal resistance, junction - case	R_{thJC}		-	-	3.6	K/W
Thermal resistance, junction - ambient, leaded	R_{thJA}		-	-	62	
SMD version, device on PCB:	R_{thJA}	minimal footprint	-	-	62	
		6 cm ² cooling area ¹⁾	-	-	40	

Electrical characteristics, at $T_j=25\text{ }^{\circ}\text{C}$, unless otherwise specified

Static characteristics

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0\text{ V}$, $I_D=-250\text{ }\mu\text{A}$	-60	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}$, $I_D=-250\text{ }\mu\text{A}$	-2.1	3	-4	
Zero gate voltage drain current	I_{DSS}	$V_{DS}=-60\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=25\text{ }^{\circ}\text{C}$	-	-0.1	-1	μA
		$V_{DS}=-60\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=150\text{ }^{\circ}\text{C}$	-	-10	-100	
Gate-source leakage current	I_{GSS}	$V_{GS}=-20\text{ V}$, $V_{DS}=0\text{ V}$	-	-10	-100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=-10\text{ V}$, $I_D=-6.2\text{ A}$	-	221	300	m Ω
Transconductance	g_{fs}	$ V_{DS} >2 I_D R_{DS(on)max}$, $I_D=-6.2\text{ A}$	2.4	4.8	-	S

¹⁾ Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical without blown air.

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Dynamic characteristics

Input capacitance	C_{iss}	$V_{GS}=0\text{ V}, V_{DS}=-25\text{ V},$ $f=1\text{ MHz}$	-	335	420	pF
Output capacitance	C_{oss}		-	105	135	
Reverse transfer capacitance	C_{rss}		-	65	95	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=-30\text{ V}, V_{GS}=-10\text{ V}, I_D=-6.2\text{ A},$ $R_G=6\ \Omega$	-	16	24	ns
Rise time	t_r		-	46	69	
Turn-off delay time	$t_{d(off)}$		-	48	72	
Fall time	t_f		-	14	21	

Gate Charge Characteristics


Gate to source charge	Q_{gs}	$V_{DD}=-48\text{ V}, I_D=-8.8\text{ A},$ $V_{GS}=0\text{ to }-10\text{ V}$	-	-1.9	-2.6	nC
Gate to drain charge	Q_{gd}		-	-5	-8	
Gate charge total	Q_g		-	-10	-13	
Gate plateau voltage	$V_{plateau}$		-	-6	-	V

Reverse Diode

Diode continuous forward current	I_S	$T_A=25\text{ °C}$	-	-	-8.8	A
Diode pulse current	$I_{S,pulse}$		-	-	-35.3	
Diode forward voltage	V_{SD}	$V_{GS}=0\text{ V}, I_F=-8.83\text{ A},$ $T_j=25\text{ °C}$	-	-1	-1.55	V
Reverse recovery time	t_{rr}	$V_R=30\text{ V}, I_F= I_S ,$ $di_F/dt=100\text{ A}/\mu\text{s}$	-	60	90	ns
Reverse recovery charge	Q_{rr}		-	100	150	nC


1 Power dissipation

$$P_{\text{tot}} = f(T_A)$$



2 Drain current


$$I_D = f(T_A); |V_{GS}| \geq 10 \text{ V}$$



3 Safe operating area

$$I_D = f(V_{DS}); T_A = 25^\circ\text{C}; D = 0$$


parameter: t_p



4 Max. transient thermal impedance

$$Z_{\text{thJA}} = f(t_p)$$


parameter: $D = t_p / T$



5 Typ. output characteristics

$$I_D = f(V_{DS}); T_j = 25^\circ\text{C}$$


parameter: V_{GS}



6 Typ. drain-source on resistance

$$R_{DS(on)} = f(I_D); T_j = 25^\circ\text{C}$$


parameter: V_{GS}



7 Typ. transfer characteristics


$$I_D = f(V_{GS}); |V_{DS}| > 2|I_D|R_{DS(on)max}$$

parameter: T_j




8 Typ. forward transconductance

$$g_{fs} = f(I_D); T_j = 25^\circ\text{C}$$




9 Drain-source on-state resistance

$$R_{DS(on)} = f(T_j); I_D = -6.2 \text{ A}; V_{GS} = -10 \text{ V}$$




10 Typ. gate threshold voltage

$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}; I_D = -250 \text{ μA}$$



11 Typ. capacitances


$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$$



12 Forward characteristics of reverse diode

$$I_F = f(V_{SD})$$


parameter: T_j



13 Avalanche characteristics

$$I_{AS}=f(t_{AV}); R_{GS}=25\ \Omega$$


parameter: $T_{j(\text{start})}$



14 Typ. gate charge


$$V_{GS}=f(Q_{\text{gate}}); I_D=-8.8\ \text{A pulsed}$$

parameter: V_{DD}



15 Drain-source breakdown voltage

$$V_{BR(DSS)}=f(T_j); I_D=-250\ \mu\text{A}$$



16 Gate charge waveforms

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2008 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office. Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.