



FASTECH® **Fastening Systems**

FASTECH AG
 Klettverschluss-Systeme
 Zurlindenstrasse 29
 CH-4133 Pratteln
 Switzerland

Tel. +41 (0) 61 915 90 90
 Fax +41 (0) 61 915 90 99
 E-Mail info@fastech.ch
 Web www.fastech.ch

Specification

Technical data

FAST-VSTRAP

Product description	base material	100% Polyamid, woven tape
	Buckles	Acetat 25 mm buckle holds 45 kg 50 mm buckle holds 70 kg
	Tape covering on the backside	Polyurethan solvent base
	Thickness of closure	3.2 mm
	Weight / m²	Loop 350g ± 10% Hook 300g ± 10%
	Color standard	Loop black, Hook red, Buckle red
Performance data	Peel strength	min. 2.4 N/cm² max. 3.4 N/cm²
	Shear strength	min. 14 N/cm² max. 15.9 N/cm²
	Diverted shear strength	min. 21 N/cm²
	Breaking strength	min. 220 N/cm²
	Life cycle (open/close)	50% loss after 10'000 cycle
	Temperatur resistance	+140° C
	Melting point	+250°C
	Shrinkage after washing	length: 2%, width: 1% (3 x 60° C)
	Electrically conductive	no
	Washable	good
	UV resistance	good
	Humidity resistance	good
	Sewing	good
	Acid resistance	resistant to alkali, dissolvents hydrocarbons and alcohol
Test's	RoHS and REACH test performed	conform