



## 6980FDWDE - 12V Cordless Impact Driver

### Light Up Your Work Surface with High Output LED Power

---

#### Features

- Powerful efficient impacting 92.5 ft.lbs. (1,110 in.lbs.) for industrial applications
- Efficient impacts per minute (0 - 3,200 IPM)
- Impact resistant magnesium alloy gear case provides increased durability
- True variable speed for smooth increase in speed and complete control to match all applications
- Powerful (2.6Ah) Ni-MH batteries have greater capacity and longer run time than any Ni-Cd battery
- Two-piece D-28R motor with dual ball bearings and externally accessible brushes for longer tool life
- Most compact design in its class with a length of only 6-3/8"
- Ergonomically designed rubberized pistol grip for complete comfort and control
- Built-in high output LED light illuminates work surface for increased visibility
- Phosphorescent rubber bumper to locate tool in low light work areas for operator convenience
- Externally accessible brushes for greater serviceability and dual ball bearings for longer tool life

#### Standard Equipment

- 2 ea. 2.6Ah (Ni-MH) Batteries 1234 (193157-5)
- Universal Charger
- 2 ea. Battery Cover (414938-7)
- Tool Case (824660-2)

#### Specifications

Capacity: Bit Shank	1/4" Hex
No Load Speed	0 - 2,600 RPM
Impacts per Minute	0 - 3,200 IPM
Maximum Torque	92.5 ft.lbs./1,110 in.lbs.
Batteries	12VDC (2.6Ah)
Length	6-3/8"
Net Weight	3.5 lbs.

