



Sample photo

**Order symbol:** TA111107  
**Product nbr:** 5814039  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074011473  
**El. number:**  
Finland: 3438268  
:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		110	110	65	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		4.3	4.3	2.6	Impact Resistance (EN 62262): IK 07
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
<b>Cover colour:</b>		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
<b>Cover screws material:</b>		Polyamide			
<b>Cover screws colour:</b>		Grey			<b>Certificates:</b>
<b>Gasket material:</b>		PUR			Fimko
<b>Temperatures:</b>					Gost R
<b>Short term:</b>		-40 ... 80 °C			
<b>Continuous:</b>		-40 ... 60 °C			
<b>Short term:</b>		-40 ... 175 °F			
<b>Continuous:</b>		-40 ... 140 °F			
<b>Accessories:</b>					
MP 1111		Mounting plate			
DRM 80		DIN-15 Mounting rail			
FP 10674		Wall fastening lug (2 pcs)			
DPS 14553		Grey sealing plug set			

