



heat exchanger, air-to-air, specific thermal output 80 W/K, 230 V AC RAL 7035, 317x 1260x 148 mm (WxHxD), degree of protection IP54

Model		
product brand name		SIVACON
product designation		air-air heat exchanger
design of the temperature control		without thermostat
design of the control cabinet cooler		Air/air
type of voltage of the operating voltage		AC
operating voltage		
• at AC at 50 Hz rated value maximum		230 V
• at AC at 60 Hz rated value maximum		230 V
Product details		
product component		
• heating		No
• thermostat		No
Mechanical Design		
height		1 260 mm
width		317 mm
depth		148 mm
installation location		Control cabinet...panels, door
Approvals Certificates		
General Product Approval		other
		Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6423-5ML80>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6423-5ML80>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6423-5ML80

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

