

910.11 SS G1/2B / G1/2 union nut DIN 16270

910.11 Robinet à poiteau PN400

Item number: 9095110

Quantity: 1 pcs.

Order code: 910.11-SS11CB-ZZZ-P32-ZZ 0

Overview: 910.11 SS G1/2B / G1/2 union nut DIN 16270
DIN-Shut-off valve
Material body: Stainless steel 1.4571
Version: without test connection, per DIN 16270 or similiar (with vent screw)
Connection process side + instrument side: G 1/2 B male + G 1/2 with nipple and union nut
Design: Form B, with nipple and union nut as well as shaft for mounting bracket
Material packing: PTFE
Permissible medium temperature: -40...+200°C
Nominal pressure: PN max. 400 bar

Details: 910.11 Robinet à poiteau PN400
ZUBEHÖR 910.11 Ventil PN 400 CrNi-Stahl 1.4571 G1/2A

DIN-Shut-off valve
Specifications according to data sheet: AC 09.02
Version: without test connection, per DIN 16270 or similiar (with vent screw)
Material body: Stainless steel 1.4571
Material packing: PTFE
Permissible medium temperature: -40...+200°C
Nominal pressure: PN max. 400 bar
Design: Form B, with nipple and union nut as well as shaft for mounting bracket
Connection process side + instrument side: G 1/2 B male + G 1/2 with nipple and union nut