

## Features

- Specialised tooth configuration ensures optimal performance across a range of steel materials with varying wall thicknesses.
- These blades provide a cutting capacity of up to 100mm.
- Compatible with all reciprocating saws featuring a 1/2" universal shank system.

## Reciprocating Saw Blade - Metal 150 x 19 x 0.9mm - Progressive Cut

RS Stock No.: 0757823



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Reciprocating Saw Blade

0757823 Reciprocating Saw Blades are engineered for fast, straight cuts through both thick and thin metal. Designed for versatility, their specialised tooth configuration ensures optimal performance across a range of steel materials with varying wall thicknesses. At 150mm in length, these blades provide a cutting capacity of up to 100mm. Compatible with all reciprocating saws featuring a 1/2" universal shank system, they deliver reliability and precision in demanding applications.

- *Manufactured with 6150 Chromium-Vanadium Spring Steel & M2 High Speed Steel Teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Pipes, Profiles and Box Section*
- *Supplied in 5pc Packs*

## General Specifications

<b>Tooth Design</b>	Side Set, Milled
<b>Type</b>	Reciprocating Saw Blade
<b>Teeth Spacing</b>	1.4mm - 3.4mm
<b>TPI</b>	8-18
<b>Thickness</b>	0.9mm
<b>Max Cut Depth</b>	100mm
<b>Cut Type</b>	Progressive Cutting
<b>Blade Material</b>	M2 High Speed Steel
<b>Body Material</b>	6150 Chromium-Vanadium Spring Steel
<b>Fitting</b>	S-Shank 1/2"
<b>Length</b>	150mm
<b>Width</b>	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	Precision Cutting	0.9mm	225mm	19mm

XXX-XXXX 0757830	Fine Cutting	0.9mm	225mm	19mm
---------------------	--------------	-------	-------	------

## Approvals

<b>Declarations</b>	REACH DoC
---------------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	RS PRO	Reciprocating Saw Blade	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	225mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories