

FR714 - PW3 FR Modaflame Hi-Vis Work Jacket

Collection: PW3

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Work HV: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre

Outer Carton: 18

Product information

Featuring the latest innovative design, this contemporary FR two tone Hi-Vis jacket is both stylish and practical. The top pocket can accommodate modern smart phone dimensions and the spacious lower pockets are zipped for extra security. Outstanding features include segmented reflective trim, hook and loop adjustable cuffs and reinforced twin stitched seams.

PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 6.4 CAL/CM², EBT 6.8 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 13034 Type PB [6]

EN ISO 20471 Class 3



Features

- Inherent flame resistant qualities will not diminish with washing
- Back vents on upper and lower back for maximum breathability
- Twin-stitched seams for extra durability
- UKCA marked
- CE certified
- Heat applied segmented reflective tape for added visibility
- 40+ UPF rated fabric to block 98% of UV rays
- 4 pockets for ample storage
- Concealed mobile phone pocket
- Radio loops for easy clipping of a radio
- Adjustable waist for a perfect fit

FR714 - PW3 FR Modaflake Hi-Vis Work Jacket

Commodity Code: 6201401019

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR714YBRS	Yellow/Black	60.0	40.0	35.0	0.9020	0.0840	5036108395927	15036108880789
FR714YBRM	Yellow/Black	60.0	40.0	35.0	0.9540	0.0840	5036108395910	15036108880772
FR714YBRL	Yellow/Black	60.0	40.0	35.0	1.0010	0.0840	5036108395903	15036108880765
FR714YBRXL	Yellow/Black	60.0	40.0	35.0	1.0440	0.0840	5036108395934	15036108880796
FR714YBRXXL	Yellow/Black	60.0	40.0	35.0	1.0490	0.0840	5036108395941	15036108880802
FR714YBRXXXL	Yellow/Black	60.0	40.0	35.0	1.0890	0.0840	5036108395958	15036108880819