

Product Data Sheet

MaxiCut® Oil™ 34-505

Colour – Coating	Grey/black
Colour – Liner	Blue
Design	3/4 coated knitwrist
Coating	NBR (Nitrile Butadiene Rubber)
Coating texture	Micro-Foam with Non-Slip Grip
Liner	UHMWPE-Glass-Nylon, Polyester, Spandex
Patent number	EP 1 608 808
Palm thickness	1.60 mm



Dimensions

Size Range	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Total glove length (+/-10 mm)	210	220	230	240	250	260
Wrist length (mm)	65	75	80	80	90	90
Wrist width (mm)	80	82	83	86	90	90
Palm width (+/-3 mm)	100	104	106	109	113	115
Over lock colour	Blue	Red	Orange	White	White	Black

EN test Results

Test	Notified Body	Result/Pass
EN ISO 21420: 2020	TÜV Rheinland	Yes
EN 388: 2016 + A1: 2018	TÜV Rheinland	4443C



Product Data Sheet

MaxiCut® Oil™ 34-505

Typical Performance Values

EN 388:2016 + A1:2018 A. Abrasion Resistance	> 8000 Cycles
EN 388:2016 + A1:2018 B. Cut Resistance	> 10.0 index
EN 388:2016 + A1:2018 C. Tear Resistance	> 75 newtons
EN 388:2016 + A1:2018 D. Puncture Resistance	> 100 newtons
EN 388:2016 + A1:2018 E. Cut Resistance ISO	≥ 10 Newton

HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Standard 100 by OEKO-TEX® (08.BH.57867)	Certified
Washable	40°
Sanitized®	Yes



Special features

Silicone free	No
---------------	----

Packaging

Pairs per poly bag	12
Poly bags per carton	6
Carton count	72
Carton dimensions (mm)	500 x 295 x 200



Product Data Sheet

MaxiCut® Oil™ 34-505

Weight

Size Range	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Glove weight / Pair (+/-6 gram)	74	82	86	98	106	114
Gross Weight (Kg)	6.5	7	7.4	8.25	8.8	9.4
Carton Weight (Kg)	1	1	1	1	1	1
Net Weight (Kg)	5.5	6	6.4	7.25	7.8	8.4

Issue date: 05.06.2018

