

Datasheet

RS Pro AVM-09 Anemometer, 45m/s Max Air Velocity

RS Stock No: **506-9666**



Product Details

RS Pro anemometer features dual LCD 4 digit display. It has a maximum air velocity of 45 m/s. This anemometer includes instant, average and maximum flow measurements. It comes with 66 mm diameter vane sensor on flexible 1 m cable.

Features and Benefits

- Dual LCD 4 digit display
- Instant, average and maximum flow measurement
- Max/Min/hold
- Auto power off
- 66 mm dia. vane sensor on flexible 1m cable
- Air temperature measurement of 0 to +45°C



ENGLISH

Specifications:

Air Velocity Resolution	0.1 m/s
Best Air Velocity Accuracy	±4%
Best Temperature Measurement Accuracy	±1%
Dimensions	168 x 88 x 26.2 mm
Height	26.2 mm
Length	168 mm
Maximum Air Velocity	45 m/s
Measurement Parameters	Air Velocity, Temperature
Power Source	Battery
Probe Type	Vane
Temperature Measurement Resolution	0.2°C
Weight	350 g
Width	88 mm
Display Type	LCD