

R1.5-5VSC-H



Ring Terminal max 1.5SQMM M5

General Information

Extended Product Type	R1.5-5VSC-H
Product ID	7TBA301300R0074
EAN	5415022400052
Catalog Description	Ring Terminal max 1.5SQMM M5
Long Description	Vinyl-Insulated Ring Terminal, Single Crimp, Length 20.8mm, Width 8mm, Diameter 4.3mm, Stud Size M5, Wire Range 0.5-1.5mm ² , Copper, Tin Plated, Temperature Range -30 to 75 Degrees C, 600V Max, Color Red

Ordering

EAN	5415022400052
Minimum Order Quantity	20000 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	0.907 g
--------------------	---------

Container Information

Package Level 1 Width	25.4 mm
Package Level 1 Height	101.6 mm
Package Level 1 Depth / Length	152.4 mm
Package Level 2 Units	16000 piece
Package Level 2 Width	152.4 mm
Package Level 2 Height	88.9 mm
Package Level 2 Depth / Length	177.8 mm
Package Level 3 Units	16000 piece
Package Level 3 Width	317.5 mm
Package Level 3 Height	203.2 mm
Package Level 3 Depth / Length	482.6 mm

Additional Information

Brand / Label	Spec-Kon
Color	Red

Material	Copper
Product Main Type	COMPRESSION TERMINALS
Product Name	Electrical Terminal
Product Type	Vinyl-Insulated Ring Terminal
UPC	786210134451

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	R1.5-5VSC-H
Instructions and Manuals	R1.5-5VSC-H

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

