



MEGA M 250-PP1

Bolt-On Fuse, Medium, 250A, Pink

Product Properties:

Explosion-proof	No
Release characteristic	Time-lag (T)
Rated voltage	32 V
Optical defect indication	Yes
Type of current	DC
Colour code	Pink
Nominal voltage DC	32 V
Max. continuous voltage DC	32 V
Number of fuses	1 .
Model	Other
Max. current (I _{max})	250 A
Nominal current	250 A
Fuse type	Mega M

Dimensions:

Width	68 mm
MOQ	1 .
Unit	pck
Rated voltage	32 V
Mounting holes	M8
Centre-to-centre distance of connections	51 mm
Thickness	9.7 mm
Length	19 mm

Approvals:

Compliance:

Conflict Minerals	Contain "Tin"
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC004122 - Strip fuse
ETIM-Release	DYNAMIC
Trademark	NECORE
Product Group	Bolt-on / Strip fuses - Pin-pac
Search Description	BOLT-ON SÄKRING, MEDIUM, 250A
Alternative SKU	MEGAM250-PP1

Logistic information:

Barcode	733117610351
Country of origin	MX
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	MEGA M 250-PP1
Taric code	85361090
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.