



Product data sheet

Power tools for trade & industry

Plier

VDE High Leverage Diagonal Side Cutter 200mm



Insulated, simple, convenient – Bosch Professional VDE high leverage diagonal side cutter – 200 mm

The most important data

Part Number 1 600 A02 NE2

Technical data

Technical data

| | |
|--------------------------------------|------------------------------------|
| Rust resistance | + |
| Pliers type | High Leverage Diagonal Side Cutter |
| One-hand usage | + |
| Anti-slip shoulders | + |
| High leverage design | + |
| Hardened cutting edges | + |
| Weight | 0.317 kg |
| Ergonomic grip handle | + |
| VDE | + |
| Soft grip | + |
| Material | Chrome Vanadium |
| Tensile strength ordinary steel wire | 1,600 N/mm ² |
| Maximum voltage | 1,000 V |



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Tested up to 10,000 volts and VDE-certified up to 1,000 volts according to DIN EN/IEC 60900
- Convenient to handle, grasp, and cut well
- Durable and robust plier head made of chrome vanadium steel

