

5 4 3 2 1

REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APVD
A	RELEASED	20/07/02	AW	WK

Note :

HOUSING: LCP WITH 30% GF, UL 94V-0, COLOR: Black.

CONTACTS: PHOSPHOR BRONZE; 0.25 THICKNESS.

Latch :BRASS.

MECHANICAL PROPERTY :

UNMATING AND MATING LIFE : 1500 CYCLES .

ELECTRIC PROPERTY :

Voltage: 250 volts AC

Current: 1.0 amperes.

Low level contact resistance: 30 mΩ

Insulation resistance:1000 MΩ, 500V DV

Dielectric withstanding voltage:500V 1Minute

TOLERANCE: ±0.05  
RECOMMENDED PCB LAYOUT  
(TOP VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± 0.50  
1 PLC ± 0.30  
2 PLC ± 0.20  
3 PLC ± 0.15  
4 PLC ± -

ANGLES ± 3°

THIRD ANGLE PROJECTION

DWN	2020/07/02
A. WU	
CHEK	2020/07/02
S. CHIEN	
APVD	2020/07/02
Abel	
PRODUCT SPEC	
—	
WEIGHT	
—	

MIC127-140-D01		Micro Bit-connector_40p 90°	SMT Au3u" LCP
Part number		Part name	
DONG GUAN YU LIANG ELECTRONICS CO., LTD			
NAME			
Micro Bit-connector_40p 90°		SMT Au3u" LCP	
LCP			
SIZE	DRAWING No.		
A4	YL-ED-0XXXX		
CUSTOMER DRAWING		SCALE 1 : 1	SHEET 1 of 1