

# Plastic tubing PLN-4X0,75-BL

Part number: 558205

FESTO



 General operating condition

## Data sheet

| Feature                                  | Value                                                                                                          |
|------------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Outside diameter                         | 4 mm                                                                                                           |
| Flow-relevant bending radius             | 25 mm                                                                                                          |
| Inside diameter                          | 2.9 mm                                                                                                         |
| Min. bending radius                      | 12 mm                                                                                                          |
| Temperature-dependent operating pressure | -0.095 MPa ... 1.4 MPa                                                                                         |
| Temperature-dependent operating pressure | -0.95 bar ... 14 bar                                                                                           |
| Temperature-dependent operating pressure | -13.775 psi ... 203 psi                                                                                        |
| Note on operating pressure               | Water: max. 0.6 MPa at 0 - 50 °C                                                                               |
| Approval                                 | German Technical Control Board (TÜV)                                                                           |
| Certificate issuing authority            | B 013277 0506 00                                                                                               |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-]<br>Water (liquid, ice-free)                                          |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                                                                                 |
| Cleanroom class                          | Element installed statically, no meaningful evaluation possible according to ISO 14644-1                       |
| Suitable for use with food               | See supplementary material information                                                                         |
| Ambient temperature                      | -30 °C ... 80 °C                                                                                               |
| Product weight according to length       | 0.0056 kg/m                                                                                                    |
| Pneumatic connection                     | For push-in connector O.D. 4 mm<br>For barbed fitting I.D. 3 mm with union nut<br>For barbed fitting I.D. 3 mm |
| Colour                                   | Blue                                                                                                           |
| Note on materials                        | RoHS-compliant                                                                                                 |
| Material tubing                          | PE                                                                                                             |