






F
E
D
C
B
A

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2025/02/22	Henry	Rev.01 To Rev.A
B	C250706	2025/05/28	Henry	$\triangle B \times 3$



- Note:
- * CC Important Dimension To Check.
 - * Waterproof Rate: IP68 (2m/1h).
 - * Body: Aluminium Alloy.
 - * Membrane: ePTFE.
 - * O-Ring: Rubber, Black.
 - * Air permeability: >3000mL/min@7kPa.
 - * $\triangle B$ Temperature: -40~150℃
 - * Recommended plate thickness: $T > 3.5\text{mm}$
 - * Recommended Installation Torque: 3~5N.m.
 - * All Parts Are RoHS Compliant.

UNIT:mm		TITLE
TOLERANCE		BREATHABLE VENT, METAL, M10
.X ±0.25		SCALE 3:1
.XX ±0.1		SIZE A4
.XXX ±0.05		SHEET 1 OF 1
ANGLES ±1°		REV. B
		WC-REV.
		CC : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	VT-BMM10ME-N08001	DRAWN BY	Henry	DATE	2025/05/28
DWG NO	VT-BMM10ME-N08001	CHECKED BY	Jerry	DATE	2025/05/28
CUSTOMER	ALTW	APPROVED BY	Fred	DATE	2025/05/28

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.