

STANDARD HALOGÈNE / GLS SHAPE, HALOGEN TYPE

■ E27 - Ø 55 x 97 mm - econRJ

CODE	REF.	V	W	W _h	
134050	HST 1008	240	18	25	
131910	HST 1010	240	28	40	
131900	HST 2010	240	28	40	Dépolie/Frosted
131911	HST 1011	240	42	60	
131901	HST 2011	240	42	60	Dépolie/Frosted
134051	HST 1013	240	52	75	
134052	HST 1015	240	70	100	
134053	HST 1017	240	105	150	



STANDARD À INCANDESCENCE / GLS SHAPE, INCANDESCENT TYPE

■ E27 - Ø 60 x 105 mm



CODE	REF.	V	W	
005020	ST 1315	12	15	
005023	ST 1325	12	25	
005021	ST 2225	12	25	Dépolie/Frosted
005002	ST 1340	12	40	
005022	ST 2241	12	40	Dépolie/Frosted
005031	ST 1341	12	60	
005035	ST 2243	12	60	Dépolie/Frosted
005045	ST 2410	24	10	Dépolie/Frosted
005090	ST 2414	24	15	
005061	ST 2416	24	15	Dépolie/Frosted
005063	ST 2426	24	25	
005062	ST 2425	24	25	Dépolie/Frosted
005098	ST 2121	24	40	
005294	ST 2422	24	40	Dépolie/Frosted
005100	ST 2122	24	60	
008042	ST 4122*	24	60	
008228	ST 4322	24	60	Four/Oven 300°C
005296	ST 2423	24	60	Dépolie/Frosted
005102	ST 2123	24	75	
005104	ST 2124	24	100	
005041	ST 2400	24	100	Dépolie/Frosted

CODE	REF.	V	W	
005038	ST 2740	27	40	
005073	ST 3240	32	40	
005082	ST 3725	36	25	Dépolie/Frosted
005067	ST 3641	36	40	
005083	ST 3740	36	40	Dépolie/Frosted
005091	ST 3660	36	60	
005084	ST 4215	42	15	Dépolie/Frosted
005086	ST 4226	42	25	
005044	ST 4225	42	25	Dépolie/Frosted
005057	ST 4240	42	40	
005037	ST 4260	42	40	Dépolie/Frosted
005047	ST 4261	42	60	
005059	ST 4258	42	60	Dépolie/Frosted
005060	ST 4200	42	100	Dépolie/Frosted
005005	ST 4915	48	15	
005008	ST 4940	48	40	
005011	ST 4960	48	60	
005013	ST 4899	48	100	

* Filament renforcé / Reinforced filament construction