

## Datasheet

### **RS Pro Star Delta Single Time Delay Relay, Screw, 3 → 120 s, SPNO, 2 Contacts, SP, 24 → 240 V ac/dc**

RS Stock No: **896-6857**



## Product Details

RS Pro star delta single time delay relay is built-in a compact design of 22.5 mm and is suitable for DIN Rail mounting. It comes with a terminal screw type and has a time range of 3 to 120 s. It has SPNO, SP contact and switch configuration with 2 contacts and supply voltage of 24 → 240 V ac/dc.

## Features and Benefits

- 22.5 mm wide
- DIN rail mounting
- Flush knobs for better security
- LED indication for runtime and relay status
- 0.3 to 120 s timing range
- Wide supply voltage range
- IP20 (terminals), IP40 (enclosure) protection

**Specifications:**

Number of Timer Functions	Single
Power Supply	External
Switch Configuration	SP
Time Increment	Seconds
Depth	100.5 mm
Length	75 mm
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-15°C
Number of Contacts	2
Width	22.5 mm
Contact Configuration	NO (Delta), NO (Star)
Current Maximum	5 A
Current Minimum	0.1 A
Maximum Voltage	240 V ac/dc
Minimum Voltage	24 V ac/dc
Mode of Operation	Star Delta
Mounting Type	DIN Rail
Supply Voltage	24 to 240 V ac/dc
Terminal Type	Screw
Time Delay	200 ms
Time Range	3 to 120 s
IP Rating	IP20, IP40