



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #1969591-9
HSG, REC, PANEL MOUNT, GWT,
SINGLE ROW, EP2.5



TE Part #1969295-4
250 FASTON HSG., REC., 2 POS,
NATRUAL



TE Part #3-1437571-0
TPA11CGRA2=SWITCH P/B N/O RED




TE Part #1-1744418-6
16 POS EP 2.5 HDR, GLOW WIRE




TE Part #226781-3
ARINC SIZE 15 SOCKET



TE Part #5-6609074-1
60DCB10B J0=F7955




TE Part #1-1734829-1
1.25 WTB HDR DIP, 11 POS



TE Part #2007815-3
IMP100S, H, V4P10C, RG, LEW39, 5.5



TE Part #3-641523-4
04P MTA156 POST CON ASSY LF



TE Part #CB5111-000
HRHF-125FR-3

Documents

Product Drawings

CABLE TIES, 11 3/4" L, 1000 PK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-604751-9_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-604751-9_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-604751-9_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2-604751-9

CABLE TIES, 11 3/4" L, 1000 PK



CABLE TIES

English