

M18 ONEFHIWF12-502X | ONE-KEY™ FUEL™ 1/2" high torque impact wrench with friction ring

Article: 4933459728



- The M18 FUEL™ high torque impact wrench with ONE-KEY™ technology delivers 1356 Nm of fastening torque in a compact size of 213 mm, which gives more access in tight spaces.
- The 4 -Mode DRIVE CONTROL™ allows the user to shift into four different speed and torque settings to maximise application versatility.
- Mode 4 bolt removal, provides a maximum nut-busting torque of 1898 Nm then shifts to 750 rpm for unmatched control when removing fasteners.
- The integrated blow counting sensor enhances the consistent repeatability of the chosen torque setting.
- ONE-KEY™ tool control enables wireless tool customisation for increased productivity and consistent results.
- ONE-KEY™ tool tracking & security offers a Cloud-based inventory management platform that supports both location tracking and theft prevention.
- 1/2" friction ring reception.

M18 ONEFHIWF12-502X	
No load speed (rpm)	0-550/0-1400/0-1750/0-1750
Voltage (V)	18
Battery pack capacity (Ah)	5.0
Battery type	Li-ion
Impact rate (ipm)	0-950/0-1750/0-2100/0-2100
Supplied in	HD Box
Charger supplied	59 min
No. of batteries supplied	2
Max. bolt diameter	M33
Article Number	4933459728
Weight with battery pack (kg)	3.3
Max. fastening torque (Nm)	130/400/1356/1356
Nut-busting torque (Nm)	1898