

FEATURES

- Contact rating 3A single, 13A twin 125V-250Vac
- Black steel housing with foot treadle and non-skid base pad
- Stainless steel construction

RS PRO Light Duty Momentary Foot Switch - Stainless Steel Case Material, Single Pole Single Throw (SPST), 3 A @ 125 V

RS Stock No.: 116-855



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO stainless steel foot switches which are available in single ([116-855](#)) and twin versions ([116-912](#)). These high-quality switches are extremely reliable and the stainless steel housing provides the added benefits of corrosion resistance.

General Specifications

Contact Configuration	Single Pole Single Throw (SPST)
Switch Operation	Momentary
Case Material	Stainless Steel
Switch Environment	Light Duty
Colour	Black, Grey
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	2.5M of 18/3 cable without plug

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Current Rating	3A @ 125V ac

Mechanical Specifications

Length	89.69mm
Height	21.62mm
Dimensions	89.69mm x 66.67mm x 21.62mm
Width	66.67mm
Weight	0.2kg

Protection Category

IP Rating	IP68
-----------	------

Approvals

Standards Met	EN 60529
Compliance/Certifications	RoHS, CE



