



ENGLISH

## Datasheet

# 32 – 152 mm bimetal Arbor

RS Stock number [215-978](#)



### Description:

Hardened cutting edge (6tpi alternate set) welded to a tough alloy steel body  
Bonded construction reduces possibility of shattering  
For use with ferrous and non ferrous metals, plastics and wood to a depth of 32mm  
14 to 30mm diameter saws require a 9.5mm arbour  
32 to 152mm diameter saws require a 9.5mm arbour  
Arbours, pilot drills and core removal tools available

### Specifications:

Bimetal: Yes  
Hex Shank Diameter: 9.5 mm  
Screw Thread: 5/8"-18UNF  
Supported Holesaw Size: 32 – 152 mm