



Connectors > PCB Connectors > PCB Headers & Receptacles > DYNAMIC 2000 HDR ASSY



PCB Connector Type: PCB Mount Header

PCB Mount Orientation: Horizontal

Connector System: Wire-to-Board

Number of Positions: 12

Number of Rows: 2

[All DYNAMIC 2000 HDR ASSY \(44\)](#)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Horizontal
Number of Positions	12
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Mating Area Plating Material Thickness	.38 μm[15 μin]
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin



Contact Current Rating (Max)	5 A
------------------------------	-----

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mating Retention	With
PCB Mount Retention Type	Retention Leg
Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polyester GF
Centerline (Pitch)	2.5 mm[.099 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box, Tube
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-1318118-6
DYNAMIC D2100 REC 12P DBL Y

Also in the Series | Dynamic 2000 Series

Connector Contacts(10)	Connector Hardware(3)	Insertion & Extraction Tools(2)	PCB Headers & Receptacles(58)
PCB Terminal Blocks(9)	Power Contacts(10)	Rectangular Power Connectors(53)	Wire-to-Board Headers & Receptacles (58)



Customers Also Bought



TE Part #1-1827864-8
DYNAMIC 1200D REC HSG 16PX
BLACK



TE Part #1649329-4
RTE24012



TE Part #CAT-D9934-A15F
Header Assembly: Wire-to-Board, 5A,
gold or tin plated



TE Part #1-1939638-7
DYNAMIC 1100D HDR ASSY H 34P
XBLACK GOLD



TE Part #178325-2
DYNAMIC D3100D HDR V 10P ASSY
AU038



TE Part #T1952160121-009
H16BPR-SGRHC-PG21-EMC-C

Documents

Product Drawings
DYNAMIC D2100 HDR H ASSY 12P Y
Japanese

CAD Files
Customer View Model
ENG_CVM_CVM_1376020-2_E.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1376020-2_E.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1376020-2_E.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Dynamic Connector D-2000 Series
Japanese
Application Specification
Japanese

Agency Approvals
Agency Approval Document

1376020-2

PCB Mount Header, Horizontal, Wire-to-Board, 12 Position, 2.5 mm [.099 in]
Centerline, Fully Shrouded, Gold (Au), Dynamic 2000 Series



English