
Cut-off wheel

A 980 TZ *SPECIAL*





Properties

Bonding agent	Synthetic resin, fibre-reinforced
Type of grain	Aluminium oxide
Bond	■■■■■■□
Aggression	■■■■■□□
Service life	■■■■■■□

Materials

Stainless steel	●
Steel	●
NF metals	●

Product benefit

Free of iron, sulfur and chlorine - Very short cutting times - Very precise and clean cuts - Low thermal load - Minimal burr formation, minimizing finish-machining - 25 pieces delivered in the Kronenflex® tub for long-lasting high-performance and moisture protection

Applications

- Plant engineering
- Apparatus and container manufacturing
- Metal construction
- Locksmith's shop
- Stainless steel processing industry
- Railing construction

Diameter x Thickness x Bore	Form	Vmax m/s	Max. RPM	Article number
4-1/2 x 1/32 x 7/8		80 m/s	13300 rpm	322182
5 x 1/32 x 7/8		80 m/s	12250 rpm	322183

Klingspor Schleifsysteme GmbH und Co. KG
Hüttenstraße 36 - 35708 Haiger - Germany
Fon + 49 (0) 2773 922-0 Fax + 49 (0) 2773 922-186
sales@klingspor.de - www.klingspor.de