

# Specifications for Nylon Cloth tape for BMP21-PLUS; BMP21; IDPAL; LABPAL

<b>Adhesive</b>	Permanent Acrylic
<b>Article No.</b>	110894
<b>Brady Material No.</b>	<a href="#">B-499</a>
<b>Material Type</b>	Nylon Cloth
<b>Colour</b>	Black on White
<b>Finish</b>	Matt
<b>Order Reference</b>	M21-500-499
<b>Printable Area - Height (mm)</b>	4800.00
<b>Printable Area - Width (mm)</b>	12.70
<b>Printer Compatibility</b>	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
<b>Size - Length (m)</b>	4.90
<b>Size - Width (mm)</b>	12.70
<b>Additional Information</b>	High adhesion, Low profile
<b>Thickness (mm)</b>	0.166
<b>Total Qty per Pack</b>	1 Roll(s) / Box
<b>Approval/Compliance</b>	UL Recognised; CSA Accepted
<b>Application</b>	Communication Cabling; Laboratory Identification; Panel Identification; Voice & Data Communication; Wire & Cable Marking
<b>Continuous vs Die Cut Labels</b>	Continuous Tape
<b>Environment</b>	Freezer; Liquid Nitrogen; Autoclave
<b>Industry</b>	Laboratory;Electrical;Healthcare;BuildingsID
<b>Laboratory Application</b>	Bottles, Flasks & Dishes;Centrifuge, Eppendorf & PCR Tubes;Conical & Large Tubes;Cryo Tubes;Cryo Vials;General Identification;Petri Dishes;Well Plates;Vials & Tubes
<b>Description</b>	Nylon cloth labels.
<b>Max. Service Temp. °C</b>	90

