



ENGLISH

Datasheet

Stock No: 196-5122

RS Pro Orange PUR Tyred Wheel, 125kg



Product Details

Orange Polyurethane Wheel, Series NPB

Double thread shielding

Wheel width 30mm

Ball bearing hub

Solid polyurethane tyre

Industrial - Polyurethane Tyre

Polyurethanes have very high load capacity, abrasion and tear resistance, soft ride and chemical resistance.
Temperature range: -30 to + 90°C.



ENGLISH

Specifications:

Load Capacity	125kg
Tyre Type	Solid
Tyre Material	PUR
Hub Material	Nylon
Features	Abrasion Resistant, Corrosion Resistant, Soft Ride & Chemical Resistance, Tear Resistance
Hub Bearing Type	Ball Bearing
Wheel Diameter	100mm
Wheel Width	30mm
Bore Diameter	8mm
Bore Length	39mm
Colour	Orange