
Xnightsbridge

DATASHEET



RW5WW / RW5CW 230V IP65 5W Fire-Rated LED Dimmable Downlight

www.mlaccessories.co.uk



MLA PART CODE	RW5WW	RW5CW
DESCRIPTION	230V IP65 5W Fire-Rated LED Dimmable Downlight	
FINISH	White	
NETT WEIGHT (KG)	0.2	
	Diameter – 85 Projection – 6	
DIMENSIONS (MM)		
	Recessed depth – 67	
CUT-OUT (MM)	72	
MINIMUM VOID (MM)	120	
WATTAGE (W)	5	
LUMENS (LM)	565 ±5%	670 ±5%
EFFICACY (LM/W)	110	127
ССТ	3000K	4000K
LED COLOUR	Warm White	Cool White
CRI	>80	
CIRCUIT WATTAGE	5.12	5.26
RUNNING CURRENT (A)	0.023	
POWER FACTOR	>0.9	
BEAM ANGLE	45°	
LIFE SPAN (HRS)	25,000	
FIRE RATING (SOLID WOOD JOIST)	Tested to 30/60/90 minutes	
INPUT VOLTAGE	Mains 230V 50Hz	
CONSTRUCTION	Aluminium & Polycarbonate	
CLASS	Class I	
IP RATING	IP65 (IP20 from above)	
DIMMABLE	Yes	
WARRANTY	3 Years	
ORIGIN OF MANUFACTURE	China	
DECLARATION OF CONFORMITY (HELD ON FILE)	Yes	
MANUFACTURED IN ACCORDANCE WITH	BS EN 60598	
EAN	5056270800623	5056270800630

DCMAR21_V3



