

BU-118**(FLAT NOSE, STAINLESS STEEL PAINTING CLAMP)**

- The BU-118 was designed to hold parts during painting or plating processes. The clip has flat smooth jaws to prevent surface damage.
- Length 2.3" (58.4 mm), Width = .4" (10mm), Height = 1.1" (28 mm)
- Jaw Opens .5" (13mm) Max.
- Clamping force at jaws is 4±.5 lbs(1.8±.2kg) at .25"(6mm) jaw spread
- Material: Clip – 304 Stainless Steel
Rivet – 304 Stainless Steel
Spring – 302 Stainless Steel
- Rating: 10 Amps
- RoHS Compliant