

FEATURES

- Locking nuts for heavy-duty applications
- Glass-filled nylon inserts.
- Grade 8 steel
- Bright zinc plated

RS PRO, M12, Bright Zinc Plated Steel Nylon Insert Lock Nut

RS Stock No.: 530-416



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, these lock nuts contain a nylon insert for safe and secure fastening. They are designed to remain secure despite conditions of severe vibration. The nut is made from grade 8 steel with a bright zinc plating, for durability and environmental resistance over a long period of use.

General Specifications

Thread Size	M12
Type	Nylon Insert
Material	Steel
Finish	Bright Zinc Plated
Grade	8
Applications	Domestic appliances such as washers and dryers, Industrial machinery, Automotive industry

Mechanical Specifications

Specification	DIN 982
Thickness	14.2mm to 14.9mm
Thread Pitch	1.75
Width Across Corners	20.03mm
Width Across Flats	17.73mm to 18 mm
Wrenching Height	8.3mm

Approvals

Compliance/Certifications	RoHS
----------------------------------	------



RS Part No.	Thread Size
524281	M3
524304	M4
524310	M5
524326	M6
530393	M8
530400	M10
530416	M12

