



Part Number : [1600746010](#)
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, UL 94V-0, Keying Option D, with Connector Position Assurance, Black
Series Number : 160074
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings


[1600746010 sd.pdf](#)
[PK-31300-903-001.pdf](#)

Specifications

[AS-33472-100-001.pdf](#)
[PS-160074-0001-001.pdf](#)
[1600742276-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160074
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, UL 94V-0, Keying Option D, with Connector Position Assurance, Black
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	191128293730

Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	18.700/g

Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	D
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Sealed Cavity Plug	<u>343450001</u>
MX150 Male Terminals	<u>33000</u>
MX150 Male Terminals	<u>33011</u>