

UPT-20, 0...6 bar gauge, G1/2B , 4...20 mA/HART, 2-W

Universal process pressure transmitter UPT

Item number: 14113645

Quantity: 1 pcs.

Order code: UPT-20-ZZZ-KAPRS-BG360-GDZS2Z-ZZ
PZZZZZZZZZZZZZZZZM1000Z-ZZFUP

Overview: UPT-20, 0...6 bar gauge, G1/2B , 4...20 mA/HART, 2-W
, 0.15%
plastic case, plastic window PC
4 1/2-digit LCD, M20x1..5 cable gland PA black 6-12mm
Scaling: ...

Details: Universal process pressure transmitter UPT
Model: UPT-20
Specifications according to data sheet: PE 86.05
power supply: DC 12...36 V / DC 14...30 V
Measuring range: adjustable with turn down up to 100 : 1
Ingress protection: IP 66/67 with pressure compensation
Process connection type: Standard connection with pressure port
Case design: plastic version, IP66/IP67
Digital Display: with integrated 4 1/2 digit LCD-display
window: plastic window PC
Output signal: 4 ... 20 mA with HART protocol, 2-wire
Electrical connection: M20x1,5 / cable gland PA black (ø6-12mm)
Measuring range: 0...6 bar gauge
Process connection: G 1/2 B
Accuracy: 0.15% of span
Sensor principle: piezoresistiv