


C44A, Film, Metallized Polypropylene, Power, 10 uF, 5%, 630 VAC, 1500 VDC



Dimensions

D	70mm +/-0.5mm
L	138mm +/-2mm
S	22.3mm +/-0.5mm

Packaging Specifications

Mounting:	Bolt - M12x12.5
Packaging:	Bulk, Bag
Packaging Quantity:	12

General Information

Supplier:	KEMET
Series:	C44A
Dielectric:	Metallized Polypropylene
Style:	Can
RoHS:	Yes
Lead:	Threaded Studs M6
Miscellaneous:	Thermal Resistance = 5.3 C/W

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	5%
Voltage AC:	630 VAC
Voltage DC:	1500 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70°C
Max dV/dt:	300 V/us
Resistance:	3 mOhms (TYP)
Ripple Current:	32 Amps, 3000 Amps (Peak)