



## ZC 712 AB-PP1

Fuse Holder, Mini, Black House, 3.31mm<sup>2</sup>, AWG12, 300mm Red Cable

### Product Properties:

Permitted cable outer temperature after assembling without vibration	-30-70 °C
Connection type	Other
Rated current	30 A
Rated voltage	58 V
Type of current	DC
Mounting method	Other

### Dimensions:

MOQ	10 .
Unit	pck
Rated voltage	58 V
Dimensions glass fuse	Blade fuse

### Approvals:

### Compliance:

Conflict Minerals	Contain "Tin"
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)

### Other information:

ETIM-Class	EC000036 - Miniature fuse holder
ETIM-Release	10.0
Trademark	NECORE
Product Group	Fuse Holder - Mini

<b>Search Description</b>	SÄKRINGSHÅLLARE, MINI
<b>Alternative SKU</b>	ZC712AB-PP1

### **Logistic information:**

<b>Barcode</b>	733117611886
<b>Country of origin</b>	TW
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	10 .
<b>Stock code</b>	ZC 712 AB-PP1
<b>Taric code</b>	85369010
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.