

Features

- Waterproof IP67 rating guarantees protection against extended immersion under higher pressures
- External cable diameter 3.5~5mm
- Voltage rating of 60V AC/DC
- Current rating of 3A
- Gold-plated bronze contacts for corrosion resistance
- Threaded mating type
- Operating temperature range from -25°C to 80°C
- PA66 black shell
- Conforms to standards IEC 61076-2-104

RS PRO Female M8 3 Pin A-code Connector

RS Stock No.: 0335206



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The 3 pin A-code female M8 plastic field wireable connector had been widely used for automotive and sensor application, it's unshielded.

General Specifications

Number of Contacts	3
Shielding	unshielded
Housing Material	PA66
Contact Material	Bronze
Contact Plating	Gold
Pole Format	3 pin
Contact Gender	Female
Mating Type	Threaded
Body Orientation	Angled
Mating Cycles	500
Cable limits	3.5-5mm OD
Typical conductor size	24AWG
Application	Sensor, automation

Electrical Specifications

Plug/Socket	Plug
Current Rating	3A
Voltage Rating	60V AC/DC
Insulation Resistance	$\geq 100M\Omega$

Mechanical Specifications

Connector Size	Standard
Termination Method	Screw
Mounting Type	/
Panel Cut-Out	/
Contact Diameter	24AWG

Operation Environment Specifications

Operating Temperature	-25°C to 80°C
-----------------------	---------------

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE, RoHS, REACH, IP67
---------------------------	-----------------------

Dimensions in mm

