

Doro PhoneEasy® 610

Easy to use clamshell mobile phone with Bluetooth

A sleek, clamshell mobile phone for answering and ending calls with a simple flip. The elegant design includes enhancements such as raised edges, soft touch coating and widely spaced, concave keys for maximum comfort and ease of use. Doro PhoneEasy® 610 is both sturdy and offers great battery life, so it will last a long time in every aspect. Other features include charging cradle, Bluetooth®, enhanced sound and security functions.

- ✓ Direct memories and SMS button
- ✓ Easy to read text and display
- ✓ Extra loud and clear sound



STANDARD FEATURES ON MOST DORO PHONES

- | | | | | | | | | | |
|--|---|---|---|---|---|--|---|---|---|
|  |  |  |  |  |  |  |  |  |  |
| Loud and clear sound | Adjustable frequency | Hearing Aid Compatible | Separated large keys | Adjustable contrast and theme | Adjustable text size | Security functions | Ergonomic design | Easy menu handling | Hide unwanted functions |

Doro PhoneEasy® 610



Main features

Speakerphone	✓
Backlit keypad	✓
FM-radio	✓
Assistance button	✓
Calculator	✓
Calendar with reminder	✓
Wake up alarm	✓
ICE (In Case of Emergency)	✓
Remote programming (OTA)	✓

Memories

Call log positions	60
One touch memories	3
Phonebook positions	300
Multiple numbers per contact	✓
List top 10 contacts first	✓

Handset unit display

Colour display	✓
Display size (H x W mm)	42*34
Resolution (H x W pixels)	220*176
Big display text	✓
Optional display modes optimised for visually impaired users	✓
Adjustable font size	✓

Sounds & Signals

Visual ring indicator	✓
Vibrating ringer	✓
Ringer volume settings except off	7
Ringer off setting	✓

Volume settings

7

Ergonomic sound™

Tone control	✓
--------------	---

SMS

SMS	✓
SMS key	✓
Predictive text	✓

Ergonomics

Hide unwanted functions	✓
Handset size (mm)	100*52*22
Handset weight including batteries (g)	103

Cables & Connections

Headset outlet (2.5mm)	✓
------------------------	---

Powering handset unit

Standby time (up to hours)	490
Talk time (up to hours)	8,7
Battery included (type)	Li-ion 800mA
Universal Charging solution (UCS)	✓

Technology

GSM (band)	850/900/1800/1900
Bluetooth®	✓
Bluetooth® protocol	2.2
VCard support	✓
SAR	0.355

Accessories



Doro PhoneEasy® 610

Acoustics

Receiving maximum level (dB RLR)	-35
Maximum receiving amplification (dB)	35
Hearing Aid Compatibility Rating	M3/T4
Maximum ringer volume (dB(A) at 1 metre)	85

Charging cradle included	✓
Headset included	✓
Lanyard included	✓