

Power Cutter LXT®

DCE090

2 x 18 V • 230 mm • 6 600 min⁻¹

Powerful Power Cutter LXT® for heavy duty use.

Water supply kit can be connected; The hose is designed to run inside the tool housing to prevent from being caught in objects. Active Feedback sensing Technology (AFT) turns the motor off if rotation speed suddenly slows or wheel is forced to stop.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	6600 min ⁻¹
Max. Depth of Cut	88 mm
Dead Man's Switch (No Lock-On)	✓
Electronic brake	✓
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	230 mm
Sound Power Level (L _{WA})	114 dB(A)
Sound Pressure Level (L _{pA})	103 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Uncertainty (K Factor)	1,5 m/s ²
Vibration Level (3 axes) at Front	5,9 m/s ²

User benefits

- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

■ Optional AC

B-12712

Diamond wheel 230 mm, Quasar



B-54025

Diamond wheel 230 mm, Nebula, Dry



B-55326

Vacuum Brazed Rescue Diamond



■ Other

User manual

Parts drawing