


## 9781 Max. 10,2 W

### AC/DC ADAPTER - UNREGULATED

- Max. 10,2 W output power
- 230 VAC input voltage
- Available with EU and UK terminals
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
  - reduced stocking requirements
  - short delivery lead times
  - snap-locks for added safety



<b><u>Technical specifications</u></b>	
<i>Input voltage:</i>	230 VAC $\pm$ 10% , 50 Hz
<i>Output voltage:</i>	12 VDC $\pm$ 10%
<i>Max.output power:</i>	10,2 W
<i>Load current:</i>	850 mA
<i>Temperature range:</i>	-10°C to +40°C
<i>Protection:</i>	Protected against internal short circuit by thermal fuse in primary
	Protected against overload and short circuit by electronic limitation of primary
<i>Insulation class</i>	II
<i>Electrical safety</i>	EN 60950
<i>EMC, Emission</i>	EN50081-1
<i>EMC, Immunity</i>	EN50082-1
<i>Mains connections:</i>	EU and UK
<i>Output terminals:</i>	Secondary cable w/snap-on plugs
<i>IP-grade</i>	40
<i>Dimensions (EU mod):</i>	58x74x48mm
<i>Weight:</i>	460g