

Soft Polyurethane, Metric Size - TUS

TUS0604BU-100

Datasheet

General series information

- Applicable tubing O.D.: Ø 4 to Ø 16 mm
- Operating temperature: -20 to 60 °C for air and 0 to 40 °C for water
- 29 colour variations.

Standard specifications

Size	0604 (O.D. Ø6 I.D. Ø4)
Color	BU (Blue)
Roll Length	100 m Roll
-	Air
Maximum operating pressure	0.6 MPa
Weight	1.930 Kg

Additional information

Catalogue

[T_EU.pdf](#)