



Cold



Medium Duty

Fully-coated and insulated nitrile gloves, ensuring outstanding comfort in cold conditions

- **Heightened durability:** By combining durable nylon and nitrile, ActivArm® 80-409 general-purpose protective gloves are able to repel water and resist wind, while protecting hands with outstanding insulation for temperatures as low as -15°C/5°F and delivering superior grip in wet conditions via a rough finish
- **Optimized comfort:** These warm insulated gloves are composed of a dual-layer and thin seamless knit, thermal terry loop acrylic liner, which grants a high level of comfort
- **Added protection:** ActivArm® 80-409 safety gloves' elastic knitwrist affords a secure fit, providing additional wrist protection for mediumweight tasks
- **Reduced risks:** These silicone-free industrial gloves ensure product protection and are suitable for food applications



Industries

- Agriculture
- Construction
- Food Processing
- Shipping

Applications

- Outdoor Winter Use
- Maintenance
- Cold Storage
- Street cleaning and refuse collection

Previously known as: PowerFlex®80-409

Key Features

- **Fully dipped nitrile coating:** Advanced abrasion resistance and grip
- **Thermal terry loop acrylic liner:** For genuinely cold-resistant gloves
- **Elastic knitwrist:** For form-fitting and comfortable hand protection

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 80-409	Finishing: Fully Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Acrylic, Polyester, Polyamide Cuff Style: Knitwrist	13	8, 9, 10	255-275 mm; 10.0-10.8 inches	Blue	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699