

## Han-Eco 6B Outd-HBM-with SL



|                    |   |
|--------------------|---|
| Part number        | 19 43 206 0340  |
| Specification      | Han-Eco 6B Outd-HBM-with SL   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19432060340">https://b2b.harting.com/19432060340</a> |

### Identification

|                          |                           |
|--------------------------|---------------------------|
| Category                 | Hoods/Housings            |
| Series of hoods/housings | Han-Eco® B                |
| Type of hood/housing     | Bulkhead mounted housings |

### Version

|              |                      |
|--------------|----------------------|
| Locking type | Single locking lever |
| Size         | 6 B                  |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP66            |

### Material properties

|  |                                     |
|--|-------------------------------------|
| Material (hood/housing)                                    | Polyamide<br>Fibre-glass reinforced |
| Colour (hood/housing)                                      | RAL 9005 (jet black)                |
| Material (seal)  | FPM                                 |
| Colour (seal)  | RAL 7001 (silver-grey)              |
| Material (locking)   | Polyamide<br>Fibre-glass reinforced |
| Colour (locking)   | RAL 9005 (jet black)                |
| Material flammability class acc. to UL 94                  | V-0                                 |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                 |

### Specifications and approvals

|                |  |
|----------------|--|
| Specifications | IEC 61984<br>EN 45545-2 R22: HL1, HL2, HL3<br>EN 45545-2 R23: HL1, HL2, HL3<br>EN 45545-2 R24: HL1, HL2, HL3 |
|----------------|--|



Pushing Performance

## Commercial data

|                                |          |
|--------------------------------|----------|
| Packaging size                 | 1        |
| Country of origin              | Germany  |
| European customs tariff number | 85389099 |