



Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: **Snap-On**  
Marker Size: **STD 17**  
Compatible Cable Diameter Range: **8.5 – 11.5 mm [ .335 – .452 in ]**  
Marker Cut: **Straight**  
Marking Details: **4**

[All STD Snap-On Markers \(957\)](#)

Features

Body Features

|              |         |
|--------------|---------|
| Marker Style | Snap-On |
| Marker Size  | STD 17  |

Dimensions

|                                 |                               |
|---------------------------------|-------------------------------|
| Compatible Cable Diameter Range | 8.5 – 11.5 mm[.335 – .452 in] |
|---------------------------------|-------------------------------|

Printer/Label Features

|                 |          |
|-----------------|----------|
| Marker Cut      | Straight |
| Marking Details | 4        |

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Method   | Box |
| Packaging Quantity | 50  |

Other

|                       |       |
|-----------------------|-------|
| Printed Marking Color | Black |
|-----------------------|-------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1768046-0  
STD17-APPLICATOR

Also in the Series | Agastat 7000



AC Relays(8)



DC Relays(33)



Electromechanical Relays(41)



## Customers Also Bought



TE Part #CAT-T3437-ST2999

[STD Snap-On Markers](#)

## Documents

**Product Drawings**

[STD17Y-4](#)

English

**Datasheets & Catalog Pages**

[STD/STB-type Snap-on Pre-printed Wire & Cable Markers](#)

English

[IDENTIFICATION SELECTION GUIDE](#)

English

[STD and STB Technical Datasheet](#)

English

**Product Specifications**

[RW-2538 STD and STB work instruction](#)

English