M18 BTP-0

M18™ COMPACT TRANSFER PUMP

- 18V transfer pump with 3.4 kg in weight, it's lighter than other corded transfer pumps with an equal performance
- With a flow rate of 1817 l/h, it can deliver 908 l of transferred water with one M18™ 5.0 Ah battery charge
- REDLINK™ intelligence can recognise when the tool stops moving water and automatically shuts itself off to avoid dry pumping
- The tool's flexible impeller and powerful motor generate a lift height up to 5.5 m and a head height up to 23 m
- ¾″ BSPT male thread reception for any standard water hose available. For the inlet, a hose with 19 mm inner diameter is recommended, for optimised performance
- To be used for water, clear of debris only
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Max. suction height (m)	5.5
Max. head height (m)	23
Max. water temperature (°C)	60
IP protection class	IP54
Thread size (mm)	19 male thread
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933471494