

Features

- Super compact mini size
- High 1000 lumen turbo
- Removable pocket clip
- Useful magnetic base
- Easy and convenient magnetic charging
- Mini size, can be clipped to a baseball cap and used as a headtorch

RS PRO LED Rechargeable Torch 1000 lumen, 70mm

RS Stock No.: 0143265



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Rechargeable Aluminium Torch

Super high power 1000 lumen mini aluminium flashlight
 Up to 96 metre beam range (turbo mode)
 With magnetic base & pocket clip
 Super compact mini size, can be clipped on to a baseball cap and used as a headtorch
 Easy and convenient magnetic charging
 Battery level and charging indicator under switch
 Magnetic 5V 1A USB Charging cable included
 Charge time approx. 1.5 hrs
 IPX4 water resistant

General Specifications

Torch Style	Torch
Rechargeable	Yes
Plug Type	USB
Lamp Type	LED
Luminosity	1000 lm
Case Material	Aluminium
Batteries	Li-Ion
Beam Type	Long range spot beam
Water Resistant	Yes, IPX4 water resistant
Length	70 mm
Colour	Black, Red

Mechanical Specifications

USB	Type-C 5V 1A charging
Battery Charge Time	1.5 hours
Cable	1m charging cable included
Battery	3.7v 16340 700mAh Li-ion battery
Dimensions	70 x 20mm
Weight	54g
Operation	<p>OPERATION Double click the switch to 'unlock' the flashlight and it will flash twice, then press for High > Medium > Low > Off.</p> <p>Hold button for 3 seconds to activate Turbo mode.</p> <p>When in 'OFF' mode, double click switch to turn the safety lock back on, it will flash twice to confirm, or automatically does this itself after 1 min of no activity.</p> <p>Turbo - 1000LM - 30 seconds > High - 500LM - 0.5hrs > Medium - 250LM - 1.5hrs > Low - 25LM - 11hrs</p>

Approvals

Declarations	RoHS EMC REACH
Standards Met	EN IEC 55015:2019+A11:2020 EN 61547:2009 IEC 62321 IPX4 IEC 62133