



6316DDU

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	80	mm	Bore diameter
D	170	mm	Outside diameter
B	39	mm	Width
r (min.)	2.1	mm	Chamfer dimension

Basic Load Ratings

Cr	135000	N	Basic dynamic load rating
C0r	86500	N	Basic static load rating

Speeds

Grease	2800	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	91	mm	Diameter of shaft abutment
da (max.)	104.5	mm	Diameter of shaft abutment
Da (max.)	159	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

fo	13.3		Factor
----	------	--	--------

Additional information

z	8		Number of Balls
Dw	28.575	mm	Ball Diameter

Mass

Mass approx.	3.67	kg	Mass approx.
--------------	------	----	--------------

