



 PRODUCT-DETAILS

2058 UK

Control push button insert DND/MUR Group
 push button Push button with LED Control
 light 2 rocker 5 ... 24 V



General Information

Extended Product Type	2058 UK
Product ID	2CKA001413A1114
EAN	4011395284681
Catalog Description	Control push button insert DND/MUR Group push button Push button with LED Control light 2 rocker 5 ... 24 V
Long Description	El. push-switch DND/MUR

Installation

Instructions and Manuals	No document needed
Wiring Diagram	2CKA000073B5089
Mounting Type	Flush Mounted
Type of Fastening	Mounting with Screw
Modular Components Included	Flush Mounted Insert with Control Element

Environmental

Ambient Air Temperature	Operation -5 ... +45 °C
Degree of Protection	IP20

Technical

Data Sheet, Technical Information	No document needed
Function	Illumination Function: Control
Number of Poles	1P
Number of Outputs	2
Number of LEDs	2
Number of Inputs	3
Number of Rocker Switches	2
Actuator Type	Push button
Lamp Type	LED Control light
Illumination	Illuminated
Lamp Color	Red / Green
Terminal Type	Screwless Terminals

Electrical

Rated Voltage (U_r)	5 ... 24 V
Rated Current (I_n)	0.05 A
Number of Contacts NO	4

Design

Design Range	Platform 63 Busch-art linear future linear Busch-axcent solo Pure Stainless Steel carat Busch-Dynasty
Design Range Variant	Busch-art linear Busch-art linear - with Decor Ring Busch-art linear - pur future future linear Busch-axcent Busch-axcent pur
Surface Finishing	Untreated Matt
Material	Plastic
Color	black

Dimensions

Product Net Width	71 mm
Product Net Height	71 mm
Product Net Depth / Length	33.8 mm

Product Net Weight	48 g
Built-In Depth (t ₂)	32 mm

Material Compliance

RoHS Declaration	2CKA200000E7574
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Declaration	2CKA309999E9999
REACH Information	False - does not contain substances > 0.1 mass percentage
REACH Date	20250901
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer

Certificates and Declarations

Declaration of Conformity - CE	2CKA200000E7574
EU Data Act Applicability and Compliance	Not Applicable

External Classifications and Standards

ETIM 9	EC000029 - Push button
ETIM 10	EC000029 - Push button
eClass	V11.0 : 27144044

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CKA001751A3220	Rocker with legend DND, MUR for Switch/push button Two-part rocker studio white - Platform 63	2058-24-84	1	piece
2CKA001751A3221	Rocker with legend DND, MUR for Switch/push button Two-part rocker aluminium silver - Platform 63	2058-24-83	1	piece
2CKA001751A3223	Rocker with legend DND, MUR for Switch/push button Two-part rocker anthracite - Platform 63	2058-24-81	1	piece
2CKA001751A3226	Rocker with legend DND, MUR for Switch/push button Two-part rocker grey metallic - Platform 63	2058-24-803	1	piece
2CKA001751A3225	Rocker with legend DND, MUR for Switch/push button Two-part rocker ivory white - Platform 63	2058-24-82	1	piece
2CKA001751A3222	Rocker with legend DND, MUR for Switch/push button Two-part rocker studio white matt - Platform 63	2058-24-884	1	piece
2CKA001751A3224	Rocker with legend DND, MUR for Switch/push button Two-part rocker black matt - Platform 63	2058-24-885	1	piece
2CKA001751A3227	Rocker with legend DND, MUR for Switch/push button Two-part rocker stainless steel - Pure Stainless Steel	2058-24-866	1	piece

2CKA001754A4536	Cover frame 1-gang studio white - solo	1721-84-500	1	piece
2CKA001754A4442	Cover frame 1-gang white glass - carat	1721-811	1	piece
2CKA001754A4600	Cover frame 1-gang ivory white - Busch-Dynasty	1721-832-500	1	piece
2CKA001754A4506	Cover frame 1-gang ivory white - future linear	1721-182K-500	1	piece
2CKA001754A4168	Cover frame 1-gang ivory white - future	1721-182	1	piece
2CKA001754A4409	Cover frame 1-gang black - Busch-axcent	1721-281	1	piece
2CKA001754A4800	Cover frame 1-gang glass black - Busch-axcent pur	1721-245	1	piece
2CKA001754A4322	Cover frame 1-gang glass black - carat	1721-825	1	piece
2CKA001754A4605	Cover frame 1-gang anthracite - Busch-Dynasty	1721-831-500	1	piece
2CKA001754A4240	Cover frame 1-gang anthracite - future linear	1721-181K	1	piece
2CKA001754A4538	Cover frame 1-gang chrome gloss - solo	1721-80G-500	1	piece
2CKA001754A4820	Cover frame 1-gang porcelain anthracite - carat	1721-815	1	piece
2CKA001754A4535	Cover frame 1-gang chrome matt - solo	1721-80-500	1	piece
2CKA001754A4254	Cover frame 1-gang stainless steel - carat	1721-860	1	piece
2CKA001754A4529	Cover frame 1-gang aluminium silver - future linear	1721-183K-500	1	piece
2CKA001754A4360	Cover frame 1-gang chrome - carat	1721-826-101	1	piece
2CKA001754A4531	Cover frame 1-gang studio white matt - future linear - matt	1721-884K-500	1	piece
2CKA001754A4356	Cover frame 1-gang gold - carat	1721-823-101	1	piece
2CKA001754A4532	Cover frame 1-gang black matt - future linear - matt	1721-885K-500	1	piece
2CKA001754A4258	Cover frame 1-gang bronze - carat	1721-821	1	piece
2CKA001754A4334	Cover frame 1-gang yellow - Busch-axcent	1721-285	1	piece
2CKA001754A4775	Cover frame 1-gang glass purple - Busch-axcent pur	1721-223	1	piece
2CKA001754A4560	Cover frame 1-gang polished brass ivory white - Busch-Dynasty	1721-838-500	1	piece
2CKA001754A4337	Cover frame 1-gang green - Busch-axcent	1721-286	1	piece
2CKA001754A4760	Cover frame 1-gang glass sun - Busch-axcent pur	1721-225	1	piece
2CKA001754A4570	Cover frame 1-gang polished brass decor ivory white - Busch-Dynasty	1721-836-500	1	piece
2CKA001754A4340	Cover frame 1-gang red - Busch-axcent	1721-287	1	piece
2CKA001754A4770	Cover frame 1-gang glass avocado - Busch-axcent pur	1721-226	1	piece
2CKA001754A4565	Cover frame 1-gang polished brass anthracite - Busch-Dynasty	1721-835-500	1	piece
2CKA001754A4343	Cover frame 1-gang blue - Busch-axcent	1721-288	1	piece
2CKA001754A4765	Cover frame 1-gang glass coral - Busch-axcent pur	1721-227	1	piece
2CKA001754A4575	Cover frame 1-gang polished brass decor anthracite - Busch-Dynasty	1721-833-500	1	piece
2CKA001754A4755	Cover frame 1-gang glass ocean - Busch-axcent pur	1721-228	1	piece
2CKA001754A4780	Cover frame 1-gang glass oyster - Busch-axcent pur	1721-229	1	piece
2CKA001754A4688	Cover frame 1-gang platinum - Busch-axcent pur	1721-270-500	1	piece
2CKA001754A4580	Cover frame 1-gang antique brass ivory white - Busch-Dynasty	1721-848-500	1	piece
2CKA001754A4708	Cover frame 1-gang black matt - Busch-axcent pur	1721-275-500	1	piece
2CKA001754A4590	Cover frame 1-gang antique brass decor ivory white - Busch-Dynasty	1721-846-500	1	piece
2CKA001754A4698	Cover frame 1-gang titanium - Busch-axcent pur	1721-276-500	1	piece

2CKA001754A4585	Cover frame 1-gang antique brass anthracite - Busch-Dynasty	1721-845-500	1	piece
2CKA001754A4595	Cover frame 1-gang antique brass decor anthracite - Busch-Dynasty	1721-843-500	1	piece
2CKA001754A4790	Cover frame 1-gang paper brown - Busch-axcent pur	1721-243	1	piece
2CKA001754A4785	Cover frame 1-gang paper blue - Busch-axcent pur	1721-248	1	piece
2CKA001754A4805	Cover frame 1-gang slate grey - Busch-axcent pur	1721-290	1	piece
2CKA001754A4795	Cover frame 1-gang concrete grey - Busch-axcent pur	1721-298	1	piece
2CKA001754A4713	Cover frame 1-gang red - future linear	1721-12-182K-101	1	piece
2CKA001754A4527	Cover frame 1-gang studio white - future linear	1721-184 NSK-500	1	piece
2CKA001754A4499	Cover frame 2-gang studio white - future linear	1722-184K-500	1	piece
2CKA001754A4501	Cover frame 2-gang stainless steel - Pure Stainless Steel	1722-866K-500	1	piece
2CKA001754A4174	Cover frame 2-gang studio white - future	1722-184	1	piece
2CKA001754A4508	Cover frame 2-gang studio white - future	1722-184-500	1	piece
2CKA001754A4332	Cover frame 2-gang studio white - Busch-axcent	1722-284	1	piece
2CKA001754A4438	Cover frame 2-gang white glass - Busch-axcent pur	1722-280	1	piece
2CKA001754A4539	Cover frame 2-gang studio white - solo	1722-84-500	1	piece
2CKA001754A4443	Cover frame 2-gang white glass - carat	1722-811	1	piece
2CKA001754A4601	Cover frame 2-gang ivory white - Busch-Dynasty	1722-832-500	1	piece
2CKA001754A4231	Cover frame 2-gang ivory white - future linear	1722-182K	1	piece
2CKA001754A4169	Cover frame 2-gang ivory white - future	1722-182	1	piece
2CKA001754A4410	Cover frame 2-gang black - Busch-axcent	1722-281	1	piece
2CKA001754A4801	Cover frame 2-gang glass black - Busch-axcent pur	1722-245	1	piece
2CKA001754A4323	Cover frame 2-gang glass black - carat	1722-825	1	piece
2CKA001754A4606	Cover frame 2-gang anthracite - Busch-Dynasty	1722-831-500	1	piece
2CKA001754A4241	Cover frame 2-gang anthracite - future linear	1722-181K	1	piece
2CKA001754A4327	Cover frame 2-gang chrome gloss - solo	1722-80G	1	piece
2CKA001754A4821	Cover frame 2-gang porcelain anthracite - carat	1722-815	1	piece
2CKA001754A4537	Cover frame 2-gang chrome matt - solo	1722-80-500	1	piece
2CKA001754A4255	Cover frame 2-gang stainless steel - carat	1722-860	1	piece
2CKA001754A4530	Cover frame 2-gang aluminium silver - future linear	1722-183K-500	1	piece
2CKA001754A4361	Cover frame 2-gang chrome - carat	1722-826-101	1	piece
2CKA001754A4415	Cover frame 2-gang studio white matt - future linear - matt	1722-884K	1	piece
2CKA001754A4357	Cover frame 2-gang gold - carat	1722-823-101	1	piece
2CKA001754A4534	Cover frame 2-gang black matt - future linear - matt	1722-885K-500	1	piece
2CKA001754A4259	Cover frame 2-gang bronze - carat	1722-821	1	piece
2CKA001754A4335	Cover frame 2-gang yellow - Busch-axcent	1722-285	1	piece
2CKA001754A4776	Cover frame 2-gang glass purple - Busch-axcent pur	1722-223	1	piece
2CKA001754A4561	Cover frame 2-gang polished brass ivory white - Busch-Dynasty	1722-838-500	1	piece
2CKA001754A4338	Cover frame 2-gang green - Busch-axcent	1722-286	1	piece
2CKA001754A4761	Cover frame 2-gang glass sun - Busch-axcent pur	1722-225	1	piece

2CKA001754A4571	Cover frame 2-gang polished brass decor ivory white - Busch-Dynasty	1722-836-500	1	piece
2CKA001754A4341	Cover frame 2-gang red - Busch-axcent	1722-287	1	piece
2CKA001754A4771	Cover frame 2-gang glass avocado - Busch-axcent pur	1722-226	1	piece
2CKA001754A4566	Cover frame 2-gang polished brass anthracite - Busch-Dynasty	1722-835-500	1	piece
2CKA001754A4344	Cover frame 2-gang blue - Busch-axcent	1722-288	1	piece
2CKA001754A4766	Cover frame 2-gang glass coral - Busch-axcent pur	1722-227	1	piece
2CKA001754A4576	Cover frame 2-gang polished brass decor anthracite - Busch-Dynasty	1722-833-500	1	piece
2CKA001754A4756	Cover frame 2-gang glass ocean - Busch-axcent pur	1722-228	1	piece
2CKA001754A4781	Cover frame 2-gang glass oyster - Busch-axcent pur	1722-229	1	piece
2CKA001754A4689	Cover frame 2-gang platinum - Busch-axcent pur	1722-270-500	1	piece
2CKA001754A4581	Cover frame 2-gang antique brass ivory white - Busch-Dynasty	1722-848-500	1	piece
2CKA001754A4709	Cover frame 2-gang black matt - Busch-axcent pur	1722-275-500	1	piece
2CKA001754A4591	Cover frame 2-gang antique brass decor ivory white - Busch-Dynasty	1722-846-500	1	piece
2CKA001754A4699	Cover frame 2-gang titanium - Busch-axcent pur	1722-276-500	1	piece
2CKA001754A4586	Cover frame 2-gang antique brass anthracite - Busch-Dynasty	1722-845-500	1	piece
2CKA001754A4596	Cover frame 2-gang antique brass decor anthracite - Busch-Dynasty	1722-843-500	1	piece
2CKA001754A4791	Cover frame 2-gang paper brown - Busch-axcent pur	1722-243	1	piece
2CKA001754A4786	Cover frame 2-gang paper blue - Busch-axcent pur	1722-248	1	piece
2CKA001754A4806	Cover frame 2-gang slate grey - Busch-axcent pur	1722-290	1	piece
2CKA001754A4796	Cover frame 2-gang concrete grey - Busch-axcent pur	1722-298	1	piece
2CKA001754A4714	Cover frame 2-gang red - future linear	1722-12-182K-101	1	piece
2CKA001754A4368	Cover frame with labelling field, horizontal with label space 2-gang studio white - future linear	1732-184 NSK	1	piece
2CKA001754A4502	Cover frame 3-gang studio white - future linear	1723-184K-500	1	piece
2CKA001754A4319	Cover frame 3-gang stainless steel - Pure Stainless Steel	1723-866K	1	piece
2CKA001754A4175	Cover frame 3-gang studio white - future	1723-184	1	piece
2CKA001754A4333	Cover frame 3-gang studio white - Busch-axcent	1723-284	1	piece
2CKA001754A4439	Cover frame 3-gang white glass - Busch-axcent pur	1723-280	1	piece
2CKA001754A4541	Cover frame 3-gang studio white - solo	1723-84-500	1	piece
2CKA001754A4444	Cover frame 3-gang white glass - carat	1723-811	1	piece
2CKA001754A4602	Cover frame 3-gang ivory white - Busch-Dynasty	1723-832-500	1	piece
2CKA001754A4232	Cover frame 3-gang ivory white - future linear	1723-182K	1	piece
2CKA001754A4170	Cover frame 3-gang ivory white - future	1723-182	1	piece
2CKA001754A4411	Cover frame 3-gang black - Busch-axcent	1723-281	1	piece
2CKA001754A4802	Cover frame 3-gang glass black - Busch-axcent pur	1723-245	1	piece

2CKA001754A4324	Cover frame 3-gang glass black - carat	1723-825	1	piece
2CKA001754A4607	Cover frame 3-gang anthracite - Busch-Dynasty	1723-831-500	1	piece
2CKA001754A4242	Cover frame 3-gang anthracite - future linear	1723-181K	1	piece
2CKA001754A4328	Cover frame 3-gang chrome gloss - solo	1723-80G	1	piece
2CKA001754A4822	Cover frame 3-gang porcelain anthracite - carat	1723-815	1	piece
2CKA001754A4540	Cover frame 3-gang chrome matt - solo	1723-80-500	1	piece
2CKA001754A4256	Cover frame 3-gang stainless steel - carat	1723-860	1	piece
2CKA001754A4533	Cover frame 3-gang aluminium silver - future linear	1723-183K-500	1	piece
2CKA001754A4362	Cover frame 3-gang chrome - carat	1723-826-101	1	piece
2CKA001754A4416	Cover frame 3-gang studio white matt - future linear - matt	1723-884K	1	piece
2CKA001754A4358	Cover frame 3-gang gold - carat	1723-823-101	1	piece
2CKA001754A4421	Cover frame 3-gang black matt - future linear - matt	1723-885K	1	piece
2CKA001754A4260	Cover frame 3-gang bronze - carat	1723-821	1	piece
2CKA001754A4336	Cover frame 3-gang yellow - Busch-axcent	1723-285	1	piece
2CKA001754A4777	Cover frame 3-gang glass purple - Busch-axcent pur	1723-223	1	piece
2CKA001754A4562	Cover frame 3-gang polished brass ivory white - Busch-Dynasty	1723-838-500	1	piece
2CKA001754A4339	Cover frame 3-gang green - Busch-axcent	1723-286	1	piece
2CKA001754A4762	Cover frame 3-gang glass sun - Busch-axcent pur	1723-225	1	piece
2CKA001754A4572	Cover frame 3-gang polished brass decor ivory white - Busch-Dynasty	1723-836-500	1	piece
2CKA001754A4342	Cover frame 3-gang red - Busch-axcent	1723-287	1	piece
2CKA001754A4772	Cover frame 3-gang glass avocado - Busch-axcent pur	1723-226	1	piece
2CKA001754A4567	Cover frame 3-gang polished brass anthracite - Busch-Dynasty	1723-835-500	1	piece
2CKA001754A4345	Cover frame 3-gang blue - Busch-axcent	1723-288	1	piece
2CKA001754A4767	Cover frame 3-gang glass coral - Busch-axcent pur	1723-227	1	piece
2CKA001754A4577	Cover frame 3-gang polished brass decor anthracite - Busch-Dynasty	1723-833-500	1	piece
2CKA001754A4757	Cover frame 3-gang glass ocean - Busch-axcent pur	1723-228	1	piece
2CKA001754A4782	Cover frame 3-gang glass oyster - Busch-axcent pur	1723-229	1	piece
2CKA001754A4690	Cover frame 3-gang platinum - Busch-axcent pur	1723-270-500	1	piece
2CKA001754A4582	Cover frame 3-gang antique brass ivory white - Busch-Dynasty	1723-848-500	1	piece
2CKA001754A4710	Cover frame 3-gang black matt - Busch-axcent pur	1723-275-500	1	piece
2CKA001754A4592	Cover frame 3-gang antique brass decor ivory white - Busch-Dynasty	1723-846-500	1	piece
2CKA001754A4700	Cover frame 3-gang titanium - Busch-axcent pur	1723-276-500	1	piece
2CKA001754A4587	Cover frame 3-gang antique brass anthracite - Busch-Dynasty	1723-845-500	1	piece
2CKA001754A4597	Cover frame 3-gang antique brass decor anthracite - Busch-Dynasty	1723-843-500	1	piece
2CKA001754A4792	Cover frame 3-gang paper brown - Busch-axcent pur	1723-243	1	piece
2CKA001754A4787	Cover frame 3-gang paper blue - Busch-axcent pur	1723-248	1	piece

2CKA001754A4807	Cover frame 3-gang slate grey - Busch-axcent pur	1723-290	1	piece
2CKA001754A4797	Cover frame 3-gang concrete grey - Busch-axcent pur	1723-298	1	piece
2CKA001754A4366	Cover frame with labelling field, vertical with label space 3-gang studio white - future linear	1723-184 NSK	1	piece
2CKA001754A4369	Cover frame with labelling field, horizontal with label space 3-gang studio white - future linear	1733-184 NSK	1	piece
2CKA001754A4238	Cover frame 4-gang studio white - future linear	1724-184K	1	piece
2CKA001754A4320	Cover frame 4-gang stainless steel - Pure Stainless Steel	1724-866K	1	piece
2CKA001754A4176	Cover frame 4-gang studio white - future	1724-184	1	piece
2CKA001754A4346	Cover frame 4-gang studio white - Busch-axcent	1724-284	1	piece
2CKA001754A4440	Cover frame 4-gang white glass - Busch-axcent pur	1724-280	1	piece
2CKA001754A4112	Cover frame 4-gang studio white - solo	1724-84	1	piece
2CKA001754A4445	Cover frame 4-gang white glass - carat	1724-811	1	piece
2CKA001754A4603	Cover frame 4-gang ivory white - Busch-Dynasty	1724-832-500	1	piece
2CKA001754A4233	Cover frame 4-gang ivory white - future linear	1724-182K	1	piece
2CKA001754A4171	Cover frame 4-gang ivory white - future	1724-182	1	piece
2CKA001754A4412	Cover frame 4-gang black - Busch-axcent	1724-281	1	piece
2CKA001754A4803	Cover frame 4-gang glass black - Busch-axcent pur	1724-245	1	piece
2CKA001754A4325	Cover frame 4-gang glass black - carat	1724-825	1	piece
2CKA001754A4608	Cover frame 4-gang anthracite - Busch-Dynasty	1724-831-500	1	piece
2CKA001754A4243	Cover frame 4-gang anthracite - future linear	1724-181K	1	piece
2CKA001754A4329	Cover frame 4-gang chrome gloss - solo	1724-80G	1	piece
2CKA001754A4107	Cover frame 4-gang chrome matt - solo	1724-80	1	piece
2CKA001754A4257	Cover frame 4-gang stainless steel - carat	1724-860	1	piece
2CKA001754A4309	Cover frame 4-gang aluminium silver - future linear	1724-183K	1	piece
2CKA001754A4363	Cover frame 4-gang chrome - carat	1724-826-101	1	piece
2CKA001754A4417	Cover frame 4-gang studio white matt - future linear - matt	1724-884K	1	piece
2CKA001754A4359	Cover frame 4-gang gold - carat	1724-823-101	1	piece
2CKA001754A4422	Cover frame 4-gang black matt - future linear - matt	1724-885K	1	piece
2CKA001754A4261	Cover frame 4-gang bronze - carat	1724-821	1	piece
2CKA001754A4348	Cover frame 4-gang yellow - Busch-axcent	1724-285	1	piece
2CKA001754A4778	Cover frame 4-gang glass purple - Busch-axcent pur	1724-223	1	piece
2CKA001754A4563	Cover frame 4-gang polished brass ivory white - Busch-Dynasty	1724-838-500	1	piece
2CKA001754A4350	Cover frame 4-gang green - Busch-axcent	1724-286	1	piece
2CKA001754A4763	Cover frame 4-gang glass sun - Busch-axcent pur	1724-225	1	piece
2CKA001754A4573	Cover frame 4-gang polished brass decor ivory white - Busch-Dynasty	1724-836-500	1	piece
2CKA001754A4352	Cover frame 4-gang red - Busch-axcent	1724-287	1	piece
2CKA001754A4773	Cover frame 4-gang glass avocado - Busch-axcent pur	1724-226	1	piece
2CKA001754A4568	Cover frame 4-gang polished brass anthracite - Busch-Dynasty	1724-835-500	1	piece
2CKA001754A4354	Cover frame 4-gang blue - Busch-axcent	1724-288	1	piece

2CKA001754A4768	Cover frame 4-gang glass coral - Busch-axcent pur	1724-227	1	piece
2CKA001754A4578	Cover frame 4-gang polished brass decor anthracite - Busch-Dynasty	1724-833-500	1	piece
2CKA001754A4758	Cover frame 4-gang glass ocean - Busch-axcent pur	1724-228	1	piece
2CKA001754A4783	Cover frame 4-gang glass oyster - Busch-axcent pur	1724-229	1	piece
2CKA001754A4691	Cover frame 4-gang platinum - Busch-axcent pur	1724-270-500	1	piece
2CKA001754A4583	Cover frame 4-gang antique brass ivory white - Busch-Dynasty	1724-848-500	1	piece
2CKA001754A4711	Cover frame 4-gang black matt - Busch-axcent pur	1724-275-500	1	piece
2CKA001754A4593	Cover frame 4-gang antique brass decor ivory white - Busch-Dynasty	1724-846-500	1	piece
2CKA001754A4701	Cover frame 4-gang titanium - Busch-axcent pur	1724-276-500	1	piece
2CKA001754A4588	Cover frame 4-gang antique brass anthracite - Busch-Dynasty	1724-845-500	1	piece
2CKA001754A4598	Cover frame 4-gang antique brass decor anthracite - Busch-Dynasty	1724-843-500	1	piece
2CKA001754A4793	Cover frame 4-gang paper brown - Busch-axcent pur	1724-243	1	piece
2CKA001754A4788	Cover frame 4-gang paper blue - Busch-axcent pur	1724-248	1	piece
2CKA001754A4808	Cover frame 4-gang slate grey - Busch-axcent pur	1724-290	1	piece
2CKA001754A4798	Cover frame 4-gang concrete grey - Busch-axcent pur	1724-298	1	piece
2CKA001754A4367	Cover frame with labelling field, vertical with label space 4-gang studio white - future linear	1724-184 NSK	1	piece
2CKA001754A4370	Cover frame with labelling field, horizontal with label space 4-gang studio white - future linear	1734-184 NSK	1	piece
2CKA001754A4517	Cover frame 5-gang studio white - future linear	1725-184K-500	1	piece
2CKA001754A4321	Cover frame 5-gang stainless steel - Pure Stainless Steel	1725-866K	1	piece
2CKA001754A4177	Cover frame 5-gang studio white - future	1725-184	1	piece
2CKA001754A4347	Cover frame 5-gang studio white - Busch-axcent	1725-284	1	piece
2CKA001754A4441	Cover frame 5-gang white glass - Busch-axcent pur	1725-280	1	piece
2CKA001754A4113	Cover frame 5-gang studio white - solo	1725-84	1	piece
2CKA001754A4604	Cover frame 5-gang ivory white - Busch-Dynasty	1725-832-500	1	piece
2CKA001754A4234	Cover frame 5-gang ivory white - future linear	1725-182K	1	piece
2CKA001754A4172	Cover frame 5-gang ivory white - future	1725-182	1	piece
2CKA001754A4413	Cover frame 5-gang black - Busch-axcent	1725-281	1	piece
2CKA001754A4804	Cover frame 5-gang glass black - Busch-axcent pur	1725-245	1	piece
2CKA001754A4609	Cover frame 5-gang anthracite - Busch-Dynasty	1725-831-500	1	piece
2CKA001754A4244	Cover frame 5-gang anthracite - future linear	1725-181K	1	piece
2CKA001754A4330	Cover frame 5-gang chrome gloss - solo	1725-80G	1	piece
2CKA001754A4108	Cover frame 5-gang chrome matt - solo	1725-80	1	piece
2CKA001754A4310	Cover frame 5-gang aluminium silver - future linear	1725-183K	1	piece
2CKA001754A4418	Cover frame 5-gang studio white matt - future linear - matt	1725-884K	1	piece

2CKA001754A4423	Cover frame 5-gang black matt - future linear - matt	1725-885K	1	piece
2CKA001754A4349	Cover frame 5-gang yellow - Busch-axcent	1725-285	1	piece
2CKA001754A4779	Cover frame 5-gang glass purple - Busch-axcent pur	1725-223	1	piece
2CKA001754A4564	Cover frame 5-gang polished brass ivory white - Busch-Dynasty	1725-838-500	1	piece
2CKA001754A4351	Cover frame 5-gang green - Busch-axcent	1725-286	1	piece
2CKA001754A4764	Cover frame 5-gang glass sun - Busch-axcent pur	1725-225	1	piece
2CKA001754A4574	Cover frame 5-gang polished brass decor ivory white - Busch-Dynasty	1725-836-500	1	piece
2CKA001754A4353	Cover frame 5-gang red - Busch-axcent	1725-287	1	piece
2CKA001754A4774	Cover frame 5-gang glass avocado - Busch-axcent pur	1725-226	1	piece
2CKA001754A4569	Cover frame 5-gang polished brass anthracite - Busch-Dynasty	1725-835-500	1	piece
2CKA001754A4355	Cover frame 5-gang blue - Busch-axcent	1725-288	1	piece
2CKA001754A4769	Cover frame 5-gang glass coral - Busch-axcent pur	1725-227	1	piece
2CKA001754A4579	Cover frame 5-gang polished brass decor anthracite - Busch-Dynasty	1725-833-500	1	piece
2CKA001754A4759	Cover frame 5-gang glass ocean - Busch-axcent pur	1725-228	1	piece
2CKA001754A4784	Cover frame 5-gang glass oyster - Busch-axcent pur	1725-229	1	piece
2CKA001754A4692	Cover frame 5-gang platinum - Busch-axcent pur	1725-270-500	1	piece
2CKA001754A4584	Cover frame 5-gang antique brass ivory white - Busch-Dynasty	1725-848-500	1	piece
2CKA001754A4712	Cover frame 5-gang black matt - Busch-axcent pur	1725-275-500	1	piece
2CKA001754A4594	Cover frame 5-gang antique brass decor ivory white - Busch-Dynasty	1725-846-500	1	piece
2CKA001754A4702	Cover frame 5-gang titanium - Busch-axcent pur	1725-276-500	1	piece
2CKA001754A4589	Cover frame 5-gang antique brass anthracite - Busch-Dynasty	1725-845-500	1	piece
2CKA001754A4599	Cover frame 5-gang antique brass decor anthracite - Busch-Dynasty	1725-843-500	1	piece
2CKA001754A4794	Cover frame 5-gang paper brown - Busch-axcent pur	1725-243	1	piece
2CKA001754A4789	Cover frame 5-gang paper blue - Busch-axcent pur	1725-248	1	piece
2CKA001754A4809	Cover frame 5-gang slate grey - Busch-axcent pur	1725-290	1	piece
2CKA001754A4799	Cover frame 5-gang concrete grey - Busch-axcent pur	1725-298	1	piece

Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Flush Mounted Inserts → Electronic Inserts



↻
360°